

VACU-Proof

SEALING LIQUID FOR STATIC AND DYNAMIC SEALS IN WATERRESISTANT WATCHES OR PRECISION DEVICES

Description

VACU-Proof is a sealing liquid for the re-sealing of sealed surfaces and gaskets or other sealants in waterresistant watches or other precision devices after their opening for services. *VACU-Proof* is suitable for all waterresistant joints (e.g. watch-case, crown-shaft, glass).

Application and dosage

To be dropped on to sealing surfaces and gaskets or other sealants. *Vacu-Proof* is ready for use.

Hotline for application consulting

Working days: Tel. ++49 (0) 7731 882-287. Email: chemlab@elma-ultrasonic.com

Safety recommendations

VACU-Proof is not classified as hazardous according to Regulation (EC) No 1272/2008 [GHS]. Observe the hints indicated in the Safety Data Sheets. Always handle chemicals with care.

Physical-chemical characterisation

The product is not miscible with water and keeps on top of water.
Density: 0,97 g/ml. Mixture of polydimethylsiloxanes.

Disposal

Recommendations:

1. Disposal regulations same as for used oil.
 2. Dispose via specialised disposal companies: European waste code: 13 02 06*, „synthetic engine, gear and lubricating oils“.
 3. Burn in suitable equipments, but according to official regulations.
- Do not discharge into the drains/surface waters/groundwater. Do not discharge into public sewage system. Do not discharge into the subsoil/soil.

Volumes, storage and transport

Available volumes: 25 ml in a flask with sealable dosage channel.
Store in closed original container. Protect from heat and direct solar radiation.
Shelf life: 5 years from date of production (see stamp on label).
ADR classification for all means of transport: no hazardous material.

Elma Hans Schmidbauer GmbH & Co KG

Kolpingstr. 1-7, D-78224 Singen

e-mail: info@elma-ultrasonic.com

Tel.: ++49 (0) 7731 882-0

Fax: ++49 (0) 7731 882-266

www.elma-ultrasonic.com

24.11.11/ P:\Produkte\PRODInfo\Produkte\englisch\word_GB\P_VACU-Proof_GB.doc